



CAT[®] SOLUTIONS FOR LANDSCAPE CONTRACTORS





SKID STEER LOADERS

A small machine with the power, comfort and versatility to get your big landscape jobs done.

MODEL	FLYWHEEL POWER (HP/KW)	OPERATING CAPACITY (LB/KG)	OPERATING WEIGHT (LB/KG)
216B SERIES 3	47/35	1,400/635	5,690/2581
226B SERIES 3	56/42	1,500/680	5,822/2641
236B SERIES 3	71/53	1,950/884	7,007/3178
242B SERIES 3	71/53	2,150/975	7,008/3179
246C	73/54	2,150/975	7,381/3348
252B SERIES 3	71/53	2,650/1202	7,861/3565
256C	82/61	2,350/1066	7,566/3432
262C	82/61	2,700/1225	7,968/3614
272C	90/67	3,250/1474	8,292/3761



MULTI TERRAIN LOADERS

Skid Steer power and versatility with traction and light footprint of rubber tracks.

MODEL	FLYWHEEL POWER (HP/KW)	OPERATING CAPACITY (LB/KG)	OPERATING WEIGHT (LB/KG)
247B SERIES 3	56/42	2,150/975	6,997/3174
257B SERIES 3	71/53	2,675/1213	8,060/3656
277C	82/61	3,200/1451	9,389/4259
287C	82/61	3,800/1724	9,874/4479
297C	90/67	4,200/1905	10,229/4640



COMPACT TRACK LOADERS

Suspended steel undercarriage for smooth ride and productivity in a variety of conditions.

MODEL	FLYWHEEL POWER (HP/KW)	OPERATING CAPACITY (LB/KG)	OPERATING WEIGHT (LB/KG)
259B SERIES 3	71/53	2,950/1338	8,934/4052
279C	82/61	3,200/1451	9,892/4487
289C	82/61	3,850/1746	10,365/4702
299C	90/67	4,150/1882	10,730/4867



MINI HYDRAULIC EXCAVATORS

Work in tight spaces with the power to dig in to landscape construction projects.

MODEL	NET POWER (HP/KW)	OPERATING WEIGHT (LB/KG)
301.8C	18/14	3,935/1785
302.5C	25/19	6,283/2850
303.5D CR	30/22	7,800/3540
304D CR	39/29	8,500/3855
305D CR	42/31	11,012/4995
305.5D CR	47/35	11,696/5305
307D	42/56	15,598/7075
308D CR	56/42	18,519/8400



COMPACT WHEEL LOADERS

Big loader features in a compact size. Compatible with many Skid Steer Cat® Work Tool attachments for added versatility.

MODEL	POWER (HP/KW)	PIN HEIGHT @ MAX LIFT (FT)	OPERATING WEIGHT (LB/KG)	OPERATING CAPACITY (YD³/M³)
906H	70/52	10' 7"	12,412/5630	1.2/0.9
907H	70/52	10' 7"	12,809/5810	1.3/1.0
908H	80/59	11' 2"	14,252/6465	1.4/1.1
914G	95/71	11' 3"	17,530/7950	1.8/1.4
IT14G	95/71	12' 6"	18,632/8450	1.6-1.8/1.2-1.4



INDUSTRIAL LOADERS

Fast, smooth box blade response with low effort.

MODEL	NET POWER (HP/KW)	OPERATING WEIGHT (LB/KG)	LIFT CAPACITY (LB/KG)
414E IL	89/66	15,400/10154	5,453/2473



BACKHOE LOADERS

Versatile machines for landscape construction and irrigation.

MODEL	NET POWER (HP/KW)	OPERATING WEIGHT (LB/KG)	LIFT CAPACITY (LB/KG)
416E	74/55	14,960/6792	14' 4" / 4360
420E/420E IT	89/66	15,474/7025	14' 4" / 4360
430E/430E IT	97/72	16,066/7294	15' 5" / 4698
450E	124/92	27,115/12300	17' 2" / 5260



TELEHANDLERS

Load and carry materials and nursery stock.

MODEL	LIFT HEIGHT	RATED LOAD CAPACITY (LB/KG)	POWER (HP/KW)	OPERATING WT (LB/KG)
TH255	5.6 M / 18' 4"	5,500/2500	84/63	10,800/4899
TH406	6.1 M / 20' 0"	8,000/3629	100-125/74.5-93.1	15,870/7200
TH407	7.3 M / 23' 9"	8,000/3629	100-125/74.5-93.1	16,980/7700



TRACK-TYPE TRACTORS

The industry standard for land clearing and dozing work.

MODEL	POWER (HP/KW)	OPERATING WEIGHT (LB/KG)	BLADE
D3K	74/55.2	17,185/7795	VPAT
D4K	84/62.6	17,961/8147	VPAT
D5K	96/71.6	20,741/9408	VPAT



EXCAVATORS

The power to dig into pools, water features and other larger landscape construction jobs.

MODEL	NET POWER (HP/KW)	OPERATING WEIGHT (LB/KG)
311D LRR	80/60	27,514/12480
312D/312D L	90/67	29,650/13450
314D LCR	90/67	31,747/14400
315D L	115/86	38,095/17280



WHEEL LOADERS

Lift height and loading capacity for nurseries, hardscape suppliers and snow removal.

MODEL	ENGINE HP (HP/KW)	PIN HEIGHT @ MAX LIFT (FT)	OPERATING WEIGHT (LB/KG)	OPERATING CAPACITY (YD³)
924H	138/96	12' 9"	25,644/11632	2.2-3.6
924Hz	138/96	12' 4"	24,180/10968	2.2-2.7
928Hz	160/111	12' 8"	27,699/12564	2.6-3.0
930H	160/111	13' 3"	28,725/13029	2.6-6.5

WHEN UPTIME MATTERS, COUNT ON CAT® FOR THE BEST IN DEALER SUPPORT



When you've got employees on the job and eager clients, you need equipment you can rely on. Whether you work on your own machines or want it done for you, your Cat Dealer keeps you up and running.

- Rapid parts availability
- Online parts ordering
- Preventive maintenance services
- Maintenance agreements
- Field service trucks

TOUGH TOOLS FOR TOUGH MACHINES

SITE PREP

Mulching • Dozing
Clearing • Moving
Grading • Sloping

INSTALLATION

Digging • Drilling
Trenching • Dozing
Breaking

CLEAN-UP

Sweeping • Hauling
Compacting • Grasping
Carrying • Backfilling


Providing Performance and Versatility With Ease of Operation

Cat Work Tool attachments are performance matched to Cat machines for optimum power and performance. A universal coupler also makes many of the attachments compatible with other machine brands. Designed and built to strict Caterpillar® standards, they carry with them a proven reputation for performance, versatility and reliability.

CAT WORK TOOL ATTACHMENTS

- | | | |
|---------------------------|-----------------------------|---------------------------|
| ■ Augers | ■ Buckets | ■ Hammers |
| ■ Backhoes | ■ <i>General Purpose</i> | ■ Landscape Tillers |
| ■ Blades | ■ <i>Multi Purpose</i> | ■ Material Handling Arms |
| <i>Angle</i> | ■ <i>Light Material</i> | ■ Mulchers |
| <i>Dozer</i> | ■ <i>Utility</i> | ■ Rakes |
| ■ Brooms | ■ <i>Digging</i> | <i>Industrial Grapple</i> |
| ■ Brushcutters | ■ <i>Ditch Cleaning</i> | <i>Landscape</i> |
| ■ Couplers | ■ <i>High Capacity</i> | <i>Power Box</i> |
| ■ Forks | ■ <i>Heavy Duty</i> | ■ Snowblowers |
| <i>Pallet</i> | ■ <i>Penetration</i> | ■ Snow Plow |
| <i>Utility</i> | ■ <i>Side Dump</i> | ■ Stump Grinders |
| <i>Industrial Grapple</i> | ■ <i>Industrial Grapple</i> | ■ Thumbs |
| <i>Utility Grapple</i> | ■ <i>Utility Grapple</i> | ■ Trenchers |
| | | ■ Vibratory Compactors |
| | | ■ Wheel Saws |

Consult your local Cat Dealer for complete Work Tool attachment availability.





USED EQUIPMENT

Your Cat Dealer carries a wide variety of used equipment from Caterpillar and other manufacturers. When you buy Cat® Certified Used Equipment, you know that your Cat Dealer stands behind your machine and provides:

- A thorough inspection
- Unmatched knowledge of Cat machines
- Unbeatable service and product support
- Financing
- Machine maintenance history
- Extended coverage options

Count on Cat Certified Used Equipment and know what you're getting.



RENTAL



Renting equipment or attachments for short-term or specialized jobs is often the most efficient option for landscape contractors.

At The Cat® Rental Store, you'll get quality equipment that's ready to go to work. You'll also find a variety of other offerings like hand tools, walk-behinds, pumps, generators and heaters for a one-stop rental source.

Contact your local Cat Rental Store for our complete line and more information.



FINANCING

Talk with your Cat Dealer about flexible finance options, including the Cat® AccessAccount. Whether you work with one Cat Dealer or several, the Cat AccessAccount gives you one account and one statement for all your parts, service and rental transactions.

www.cataccessaccount.com

www.cat.com/landscaping

1-800-RENT-CAT

1-888-OWN-A-CAT

