



# CAT<sup>®</sup> SOLUTIONS FOR GENERAL CONSTRUCTION CONTRACTORS



**CATERPILLAR<sup>®</sup>**



## SKID STEER LOADERS

A small machine with the power, comfort and versatility to get any job done.

MODEL	FLYWHEEL POWER (HP / KW)	OPERATING CAPACITY (LB / KG)	OPERATING WEIGHT (LB / KG)
216B SERIES 2	47 / 35	1,400 / 635	5,609 / 2581
226B SERIES 2	56 / 42	1,500 / 680	5,822 / 2641
232B SERIES 2	56 / 42	1,900 / 861	6,737 / 3056
236B SERIES 2	71 / 53	1,950 / 884	7,007 / 3178
242B SERIES 2	56 / 42	2,100 / 952	6,914 / 3136
246C	73 / 54	2,150 / 975	7,381 / 3348
252B SERIES 2	71 / 53	2,500 / 1134	7,861 / 3565
256C	82 / 61	2,350 / 1066	7,566 / 3432
262C	82 / 61	2,700 / 1225	7,968 / 3614
272C	90 / 67	3,250 / 1474	8,292 / 3761



## MULTI TERRAIN LOADERS

Skid steer power and versatility with traction and light footprint of rubber tracks.

MODEL	FLYWHEEL POWER (HP / KW)	OPERATING CAPACITY (LB / KG)	OPERATING WEIGHT (LB / KG)
247B SERIES 2	56 / 42	2,050 / 929	6,997 / 3174
257B SERIES 2	56 / 42	2,500 / 1134	7,952 / 3607
277C	82 / 61	3,212 / 1457	9,389 / 4259
287C	82 / 61	3,854 / 1748	9,874 / 4479
297C	90 / 67	4,233 / 1920	10,229 / 4640



## COMPACT TRACK LOADERS

Suspended steel undercarriage for smooth ride and productivity in variety of conditions.

MODEL	FLYWHEEL POWER (HP / KW)	OPERATING CAPACITY (LB / KG)	OPERATING WEIGHT (LB / KG)
279C	82 / 61	3,200 / 1451	9,892 / 4487
289C	82 / 61	3,850 / 1746	10,365 / 4702
299C	90 / 67	4,150 / 1882	10,730 / 4867



## MINI HYDRAULIC EXCAVATORS

Work in tight spaces with the power to dig into any construction projects.

MODEL	NET POWER (HP / KW)	OPERATING WEIGHT (LB / KG)
301.8C	18 / 14	3,935 / 1785
302.5C	25 / 19	6,283 / 2850
303C CR	30 / 22	7,837 / 3555
303.5C CR	39 / 29	8,620 / 3910
304C CR	42 / 31	10,847 / 4920
305C CR	47 / 35	11,729 / 5320
307D	42 / 56	15,598 / 7075
308D CR	56 / 42	18,519 / 8400



## COMPACT WHEEL LOADERS

Big loader features in a compact size. Compatible with many Skid Steer Loader attachments for added versatility.

MODEL	POWER (HP / KW)	PIN HEIGHT @ MAX LIFT (FT)	OPERATING WEIGHT (LB / KG)	OPERATING CAPACITY (YD <sup>3</sup> / M <sup>3</sup> )
904B	52 / 39	10' 3"	9,810 / 4450	0.78 / 0.6
906H	70 / 52	10' 7"	12,412 / 5630	1.2 / 0.9
907H	70 / 52	10' 7"	12,809 / 5810	1.3 / 1
908H	80 / 59	11' 2"	14,252 / 6465	1.4 / 1.1
IT14G	95 / 71	12' 6"	18,632 / 8450	1.6 - 1.8 / 1.2 - 1.4



## INDUSTRIAL LOADERS

Fast, smooth box blade response with low effort.

MODEL	NET POWER (HP / KW)	OPERATING WEIGHT (LB / KG)	LIFT CAPACITY (LB / KG)
414E IL	89 / 66	15,400 / 10154	5,453 / 2473



## BACKHOE LOADERS

Best-in-class performance from the most versatile machines on the construction site.

MODEL	NET POWER (HP / KW)	OPERATING WEIGHT (LB / KG)	DIG DEPTH (FT-IN / MM)
416E	74 / 55	14,960 / 6792	14'4" / 4360
420E/420E IT	89 / 66	15,474 / 7025	14'4" / 4360
430E/430E IT	97 / 72	16,066 / 7294	15'5" / 4698
450E	124 / 92	27,115 / 12300	17'2" / 5260



## TELEHANDLERS

The power to lift and extend heavy loads and place them in elevated areas of the jobsite.

MODEL	LIFT HEIGHT	RATED LOAD CAPACITY (LB / KG)	OPERATING WT (LB / KG)
TH255	5.6 m / 18'4"	5,500 / 2500	10,800 / 4899
TH406	6.1 m / 20'0"	8,150 / 3700	15,875 / 7200
TH407	7.3 m / 24'0"	8,150 / 3700	16,980 / 7700
TL642	12.8 m / 42'0"	6,500 / 2948	20,240 / 9180
TL642 w/ stabilizers	12.8 m / 42'0"	6,500 / 2948	20,920 / 9489
TL943	13.1 m / 43'0"	9,000 / 4082	26,050 / 11814
TL943 w/ stabilizers	13.1 m / 43'0"	9,000 / 4082	27,060 / 12274
TL1055	16.8 m / 55'0"	10,000 / 4536	34,910 / 15832
TL1255	16.8 m / 55'0"	12,000 / 5443	35,650 / 16168



## TRACK-TYPE TRACTORS

The industry standard for land clearing and dozing work.

MODEL	POWER (HP / KW)	OPERATING WEIGHT (LB / KG)	BLADE
D3K	74 / 55.2	17,185 / 7795	VPAT
D4K	84 / 62.6	17,961 / 8147	VPAT
D5K	96 / 71.6	20,741 / 9408	VPAT
D6K	125 / 93.2	28,409 / 12886	VPAT



## EXCAVATORS

Unmatched productivity for trenching, digging foundations or site prep.

MODEL	NET POWER (HP / KW)	OPERATING WEIGHT (LB / KG)
311D LRR	80 / 60	27,514 / 12480
312D/312D L	90 / 67	29,650 / 13450
314D LCR	90 / 67	31,747 / 14400
315D L	115 / 86	38,095 / 17280



## WHEEL LOADERS

Superior reach, excellent visibility and low effort controls to lift, load, move and dump.

MODEL	ENGINE HP (HP / KW)	PIN HEIGHT @ MAX LIFT (FT)	OPERATING WEIGHT (LB / KG)	OPERATING CAPACITY (YD <sup>3</sup> )
924H	138 / 96	12' 9"	25,644 / 11632	2.2 - 3.6
924HZ	138 / 96	12' 4"	24,180 / 10968	2.2 - 2.7
928HZ	160 / 111	12' 8"	27,699 / 12564	2.6 - 3.0
930H	160 / 111	13' 3"	28,725 / 13029	2.6 - 6.5

# WHEN UPTIME MATTERS, COUNT ON CAT<sup>™</sup> FOR THE BEST IN DEALER SUPPORT



When you've got employees on the job and eager clients, you need equipment you can rely on. Whether you work on your own machines or want it done for you, your Cat<sup>®</sup> Dealer keeps you up and running.

- Rapid parts availability
- Online parts ordering
- Preventive maintenance services
- Maintenance agreements
- Field service trucks

## TOUGH TOOLS FOR TOUGH MACHINES

### CLEARING

Ripping • Grubbing  
Breaking • Cutting  
Grabbing • Loading

### EARTHMOVING

Trenching • Excavating  
Drilling • Backfilling  
Grading • Raking

### FINISHING

Unloading • Placing  
Spreading • Compacting  
Rolling • Sweeping

### Providing Performance and Versatility with Ease of Operation

Cat Work Tool attachments are performance matched to Cat machines for optimum power and performance. A universal coupler also allows many of the attachments to be used with other machine brands. Designed and built to strict Caterpillar standards, they carry with them a proven reputation for performance, versatility and reliability.

## CAT WORK TOOLS

- Augers
- Backhoes
- Blades
  - Angle
  - Dozer
- Brooms
- Brushcutters
- Couplers
- Cold Planers
- Forks
  - Pallet
  - Utility
  - Industrial Grapple
  - Utility Grapple
- Buckets
  - General Purpose
  - Multi Purpose
  - Light Material
  - Utility
  - Digging
  - Ditch Cleaning
  - High Capacity
  - Heavy Duty
  - Penetration
  - Side Dump
  - Industrial Grapple
  - Utility Grapple
- Hammers
- Landscape Tillers
- Material Handling Arms
- Mulchers
- Rakes
  - Industrial Grapple
  - Landscape
  - Power Box
- Shears
- Snowblowers
- Snow Plow
- Stump Grinders
- Thumbs
- Trenchers
- Vibratory Compactors
- Wheel Saws

Consult your local Cat Dealer for complete Work Tool attachment availability.





## USED EQUIPMENT

Your Cat Dealer carries a wide variety of used equipment from Caterpillar and other manufacturers. When you buy a Cat Certified Used Machine, you know that your Cat Dealer stands behind it and provides:

- A thorough inspection
- Unmatched knowledge of Cat machines
- Unbeatable service and product support
- Financing
- Machine maintenance history
- Extended coverage options available

Count on Cat Certified Used Equipment and know what you're getting.



## RENTAL



Renting equipment or Work Tool attachments for short term or specialized jobs is often the most efficient option for general construction contractors.

At The Cat Rental Store™, you'll get quality equipment that's ready to go to work. You'll also find a variety of other offerings like hand tools, walk-behinds, pumps, generators and heaters for a one-stop rental source.

Contact your local Cat Rental Store for the complete line card and more information.



## FINANCING

Talk with your Cat Dealer about flexible finance options, including the Cat® AccessAccount. Whether you work with one Cat Dealer or several, the Cat AccessAccount gives you one account and one statement for all your parts, service, Work Tool attachments and rental transactions.

[WWW.CATACCESSACCOUNT.COM](http://WWW.CATACCESSACCOUNT.COM)

[WWW.CAT.COM/GENERAL-CONSTRUCTION](http://WWW.CAT.COM/GENERAL-CONSTRUCTION)

1-800-RENT-CAT

1-888-OWN-A-CAT